

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256352

Luminaire Tested: P3AS02R609040DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609040DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 313.9 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256352

CATALOG NUMBER: P3AS02R609040DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1256352

CATALOG NUMBER: P3AS02R609040DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	72	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82274
5°	77658
10°	75639
15°	73916
20°	68723
25°	61431
30°	46919
35°	27090
40°	10505
45°	4373
50°	955
55°	153
60°	132
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4373 cd/sqm

TEST NUMBER: P1256352

CATALOG NUMBER: P3AS02R609040DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	10.6
10°-20°	90.7	28.9
20°-30°	113.6	36.2
30°-40°	63.5	20.2
40°-50°	12.0	3.8
50°-60°	0.6	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.6	75.7
0°-40°	301.1	95.9
0°-60°	313.8	99.9
0°-90°	313.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	313.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	375	
5°	353	33
15°	326	91
25°	254	114
35°	101	64
45°	14	12
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256352

CATALOG NUMBER: P3AS02R609040DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	375.2
1°	373.7
2°	368.8
3°	363.0
4°	357.6
5°	352.8
6°	349.2
7°	346.2
8°	343.9
9°	341.7
10°	339.7
11°	337.8
12°	335.6
13°	332.9
14°	329.7
15°	325.6
16°	320.6
17°	315.0
18°	308.5
19°	301.2
20°	294.5
21°	287.3
22°	279.9
23°	272.0
24°	263.4
25°	253.9
26°	242.8
27°	230.3
28°	216.3
29°	201.4
30°	185.3
31°	169.2
32°	152.5
32.5°	143.3
33°	135.1
34°	118.0
35°	101.2
36°	86.1
37°	70.0
37.5°	62.7
38°	55.5
39°	44.7
40°	36.7
42.5°	22.3
45°	14.1

TEST NUMBER: P1256352

CATALOG NUMBER: P3AS02R609040DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.8
50°	2.8
52.5°	0.6
55°	0.4
57.5°	0.3
60°	0.3
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)