

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256418

Luminaire Tested: P3AS02R709040DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709040DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 188.0 lumens
Efficiency: N/A
Efficacy: 52.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256418
CATALOG NUMBER: P3AS02R709040DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1256418
 CATALOG NUMBER: P3AS02R709040DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44097
5°	43297
10°	40814
15°	37049
20°	32413
25°	27340
30°	22383
35°	17373
40°	12423
45°	7877
50°	3923
55°	2409
60°	2061
65°	1920
70°	1667
75°	1525
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7877 cd/sqm



TEST NUMBER: P1256418
 CATALOG NUMBER: P3AS02R709040DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.4	9.8
10°-20°	45.4	24.1
20°-30°	51.7	27.5
30°-40°	40.5	21.5
40°-50°	19.9	10.6
50°-60°	6.1	3.3
60°-70°	3.6	1.9
70°-80°	1.9	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.5	61.4
0°-40°	155.9	82.9
0°-60°	181.9	96.7
0°-90°	188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	188.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	201	
5°	197	18
15°	163	45
25°	113	52
35°	65	40
45°	25	20
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1256418
CATALOG NUMBER: P3AS02R709040DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	201.1
2.5°	200.1
5°	196.7
7.5°	191.2
10°	183.3
12.5°	174.2
15°	163.2
17.5°	151.4
20°	138.9
22.5°	125.8
25°	113.0
27.5°	100.4
30°	88.4
32.5°	76.4
35°	64.9
37.5°	53.9
40°	43.4
42.5°	33.7
45°	25.4
47.5°	17.8
50°	11.5
52.5°	7.6
55°	6.3
57.5°	5.5
60°	4.7
62.5°	4.2
65°	3.7
67.5°	3.1
70°	2.6
72.5°	2.1
75°	1.8
77.5°	1.6
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)