

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257043

Luminaire Tested: P3AS09R409040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 917.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257043

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257043

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	405757
5°	393968
10°	357531
15°	295371
20°	213052
25°	131790
30°	71353
35°	36861
40°	20066
45°	11226
50°	5629
55°	4205
60°	3815
65°	3684
70°	3526
75°	3304
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11226 cd/sqm

TEST NUMBER: P1257043

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.0	18.0
10°-20°	354.3	38.6
20°-30°	252.8	27.6
30°-40°	93.1	10.2
40°-50°	29.3	3.2
50°-60°	10.2	1.1
60°-70°	7.0	0.8
70°-80°	4.1	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.1	84.2
0°-40°	865.2	94.3
0°-60°	904.7	98.7
0°-90°	917.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	917.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1850	
5°	1790	165
15°	1301	354
25°	545	253
35°	138	93
45°	36	29
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1257043

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1850.4
2.5°	1836.3
5°	1789.8
7.5°	1712.7
10°	1605.7
12.5°	1469.5
15°	1301.1
17.5°	1112.2
20°	913.0
22.5°	717.0
25°	544.7
27.5°	399.8
30°	281.8
32.5°	197.6
35°	137.7
37.5°	97.6
40°	70.1
42.5°	50.4
45°	36.2
47.5°	24.4
50°	16.5
52.5°	11.8
55°	11.0
57.5°	10.2
60°	8.7
62.5°	7.9
65°	7.1
67.5°	6.3
70°	5.5
72.5°	4.7
75°	3.9
77.5°	3.1
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)