

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257044

Luminaire Tested: P3AS09R409040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 578.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257044

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257044

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179986
5°	176337
10°	164170
15°	143088
20°	115323
25°	86449
30°	60769
35°	39806
40°	24102
45°	14389
50°	8597
55°	6920
60°	6228
65°	5292
70°	5065
75°	3982
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1257044

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	12.9
10°-20°	173.6	30.0
20°-30°	163.6	28.3
30°-40°	94.6	16.4
40°-50°	37.7	6.5
50°-60°	16.7	2.9
60°-70°	10.3	1.8
70°-80°	5.4	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.6	71.2
0°-40°	506.2	87.6
0°-60°	560.6	97.0
0°-90°	578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	821	
5°	801	74
15°	630	174
25°	357	164
35°	149	95
45°	46	38
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1257044

CATALOG NUMBER: P3AS09R409040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	820.8
2.5°	816.0
5°	801.1
7.5°	773.5
10°	737.3
12.5°	688.6
15°	630.3
17.5°	565.0
20°	494.2
22.5°	423.4
25°	357.3
27.5°	295.9
30°	240.0
32.5°	191.2
35°	148.7
37.5°	112.5
40°	84.2
42.5°	63.0
45°	46.4
47.5°	33.8
50°	25.2
52.5°	20.5
55°	18.1
57.5°	16.5
60°	14.2
62.5°	11.8
65°	10.2
67.5°	8.7
70°	7.9
72.5°	6.3
75°	4.7
77.5°	3.9
80°	3.1
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)