

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256445

Luminaire Tested: P3AS05R109040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256445
CATALOG NUMBER: P3AS05R109040DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1256445
 CATALOG NUMBER: P3AS05R109040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	93	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	88	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	85	85	83
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	81	81	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	75	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	76	73	78	75	73	73	73	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	70	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	68	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408344
5°	362469
10°	251721
15°	148854
20°	84777
25°	48462
30°	26814
35°	14295
40°	7901
45°	4280
50°	2661
55°	2103
60°	1798
65°	1660
70°	1475
75°	1525
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4280 cd/sqm



TEST NUMBER: P1256445
 CATALOG NUMBER: P3AS05R109040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	29.3
10°-20°	184.8	38.7
20°-30°	95.2	19.9
30°-40°	35.7	7.5
40°-50°	11.7	2.4
50°-60°	5.0	1.0
60°-70°	3.2	0.7
70°-80°	1.9	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.0	87.9
0°-40°	455.7	95.3
0°-60°	472.4	98.8
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1862	
5°	1647	140
15°	656	185
25°	200	95
35°	53	36
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1256445
CATALOG NUMBER: P3AS05R109040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1862.2
1°	1858.5
2°	1834.1
3°	1787.6
4°	1726.3
5°	1646.7
6°	1556.4
7°	1457.4
8°	1347.4
9°	1238.7
10°	1130.5
12.5°	869.8
15°	655.7
17.5°	490.9
20°	363.3
22.5°	271.2
25°	200.3
27.5°	146.0
30°	105.9
32.5°	75.1
35°	53.4
37.5°	38.2
40°	27.6
42.5°	19.8
45°	13.8
47.5°	10.1
50°	7.8
52.5°	6.4
55°	5.5
57.5°	4.6
60°	4.1
62.5°	3.7
65°	3.2
67.5°	2.8
70°	2.3
72.5°	2.3
75°	1.8
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)