

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257061

Luminaire Tested: P3AS09R459040DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459040DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 683.0 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257061

CATALOG NUMBER: P3AS09R459040DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1257061

CATALOG NUMBER: P3AS09R459040DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144813
5°	142240
10°	134600
15°	122770
20°	108556
25°	94264
30°	80924
35°	67432
40°	50237
45°	30763
50°	14226
55°	11125
60°	10701
65°	9806
70°	9104
75°	8642
80°	7956
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30763 cd/sqm

TEST NUMBER: P1257061

CATALOG NUMBER: P3AS09R459040DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.4	8.8
10°-20°	150.6	22.0
20°-30°	178.9	26.2
30°-40°	155.4	22.8
40°-50°	77.9	11.4
50°-60°	27.1	4.0
60°-70°	19.0	2.8
70°-80°	10.6	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.8	57.1
0°-40°	545.2	79.8
0°-60°	650.2	95.2
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	646	60
15°	541	151
25°	390	179
35°	252	155
45°	99	78
55°	29	27
65°	19	19
75°	10	11
85°	2	3
90°	0	

TEST NUMBER: P1257061

CATALOG NUMBER: P3AS09R459040DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	660.4
2.5°	657.2
5°	646.2
7.5°	628.9
10°	604.5
12.5°	574.6
15°	540.8
17.5°	503.0
20°	465.2
22.5°	426.6
25°	389.6
27.5°	354.2
30°	319.6
32.5°	286.5
35°	251.9
37.5°	214.9
40°	175.5
42.5°	137.0
45°	99.2
47.5°	65.3
50°	41.7
52.5°	32.3
55°	29.1
57.5°	26.8
60°	24.4
62.5°	22.0
65°	18.9
67.5°	16.5
70°	14.2
72.5°	11.8
75°	10.2
77.5°	7.9
80°	6.3
82.5°	4.7
85°	2.4
87.5°	1.6
90°	0.0

(END OF REPORT)