

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257080

Luminaire Tested: P3AS09R509040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1093.0 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257080

CATALOG NUMBER: P3AS09R509040DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257080

CATALOG NUMBER: P3AS09R509040DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	381965
5°	371780
10°	354792
15°	321205
20°	277877
25°	227941
30°	130932
35°	40662
40°	10935
45°	3814
50°	921
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3814 cd/sqm

TEST NUMBER: P1257080

CATALOG NUMBER: P3AS09R509040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.2	14.5
10°-20°	392.0	35.9
20°-30°	412.0	37.7
30°-40°	117.9	10.8
40°-50°	11.5	1.1
50°-60°	1.0	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	962.3	88.0
0°-40°	1080.2	98.8
0°-60°	1092.7	100.0
0°-90°	1093.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1093.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1742	
5°	1689	158
15°	1415	392
25°	942	412
35°	152	118
45°	12	12
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1257080

CATALOG NUMBER: P3AS09R509040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1741.9
1°	1739.2
2°	1731.5
3°	1720.3
4°	1705.2
5°	1689.0
6°	1671.7
7°	1653.2
8°	1635.8
9°	1615.8
10°	1593.4
11°	1567.6
12°	1537.9
13°	1500.9
14°	1460.8
15°	1414.9
16°	1366.3
17°	1319.2
18°	1271.0
19°	1228.6
20°	1190.8
21°	1154.6
22°	1113.3
23°	1065.9
24°	1010.3
25°	942.1
26°	868.0
27°	785.5
28°	703.4
29°	614.7
30°	517.1
31°	425.7
32°	341.7
32.5°	305.0
33°	268.0
34°	205.5
35°	151.9
36°	111.4
37°	82.9
37.5°	71.7
38°	62.1
39°	48.2
40°	38.2
42.5°	21.6
45°	12.3



TEST NUMBER: P1257080

CATALOG NUMBER: P3AS09R509040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.9
50°	2.7
52.5°	1.2
55°	0.8
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)