

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257097

Luminaire Tested: P3AS09R509040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 886.0 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257097

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257097

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	282083
5°	276403
10°	258891
15°	231761
20°	195037
25°	148847
30°	96749
35°	57366
40°	33148
45°	16622
50°	6175
55°	4817
60°	4473
65°	4099
70°	4039
75°	3982
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16622 cd/sqm

TEST NUMBER: P1257097

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	13.2
10°-20°	282.3	31.9
20°-30°	277.0	31.3
30°-40°	139.5	15.7
40°-50°	44.1	5.0
50°-60°	11.4	1.3
60°-70°	8.1	0.9
70°-80°	5.0	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.1	76.3
0°-40°	815.7	92.1
0°-60°	871.2	98.3
0°-90°	886.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	886.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1286	
5°	1256	117
15°	1021	282
25°	615	277
35°	214	140
45°	54	44
55°	13	11
65°	8	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1257097

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1286.4
2.5°	1278.5
5°	1255.7
7.5°	1214.7
10°	1162.7
12.5°	1095.8
15°	1020.9
17.5°	934.3
20°	835.8
22.5°	729.5
25°	615.2
27.5°	493.9
30°	382.1
32.5°	287.5
35°	214.3
37.5°	158.3
40°	115.8
42.5°	81.9
45°	53.6
47.5°	30.7
50°	18.1
52.5°	13.4
55°	12.6
57.5°	11.0
60°	10.2
62.5°	9.5
65°	7.9
67.5°	7.1
70°	6.3
72.5°	5.5
75°	4.7
77.5°	3.9
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)