

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256516

Luminaire Tested: P3AS05R159040DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159040DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 332.0 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256516
CATALOG NUMBER: P3AS05R159040DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1256516
 CATALOG NUMBER: P3AS05R159040DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143168
5°	132313
10°	105632
15°	79796
20°	60765
25°	46309
30°	33170
35°	21656
40°	13282
45°	8032
50°	5322
55°	4129
60°	3552
65°	3061
70°	2757
75°	2711
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8032 cd/sqm



TEST NUMBER: P1256516
 CATALOG NUMBER: P3AS05R159040DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	16.0
10°-20°	98.2	29.6
20°-30°	87.5	26.3
30°-40°	51.8	15.6
40°-50°	21.2	6.4
50°-60°	10.0	3.0
60°-70°	6.1	1.8
70°-80°	3.2	1.0
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.0	72.0
0°-40°	290.7	87.6
0°-60°	321.9	97.0
0°-90°	332.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	332.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	653	
5°	601	53
15°	352	98
25°	191	87
35°	81	52
45°	26	21
55°	11	10
65°	6	6
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1256516
CATALOG NUMBER: P3AS05R159040DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	652.9
1°	651.3
2°	646.4
3°	636.7
4°	620.5
5°	601.1
6°	580.1
7°	555.3
8°	529.4
9°	503.0
10°	474.4
12.5°	409.2
15°	351.5
17.5°	301.9
20°	260.4
22.5°	223.7
25°	191.4
27.5°	160.1
30°	131.0
32.5°	104.6
35°	80.9
37.5°	62.0
40°	46.4
42.5°	34.5
45°	25.9
47.5°	19.9
50°	15.6
52.5°	12.9
55°	10.8
57.5°	9.2
60°	8.1
62.5°	7.0
65°	5.9
67.5°	5.4
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)