

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257103

Luminaire Tested: P3AS09R559040DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257103
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559040DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1048.1 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257103
CATALOG NUMBER: P3AS09R559040DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1257103
 CATALOG NUMBER: P3AS09R559040DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290678
5°	287959
10°	299527
15°	295371
20°	272370
25°	221626
30°	134603
35°	46605
40°	13311
45°	6357
50°	2695
55°	1223
60°	1403
65°	1245
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6357 cd/sqm



TEST NUMBER: P1257103
 CATALOG NUMBER: P3AS09R559040DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	12.1
10°-20°	361.6	34.5
20°-30°	403.1	38.5
30°-40°	131.9	12.6
40°-50°	17.4	1.7
50°-60°	3.7	0.4
60°-70°	2.2	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	891.2	85.0
0°-40°	1023.1	97.6
0°-60°	1044.2	99.6
0°-90°	1048.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1326	
5°	1308	126
15°	1301	362
25°	916	403
35°	174	132
45°	20	17
55°	3	4
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1257103
CATALOG NUMBER: P3AS09R559040DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1325.6
2.5°	1316.1
5°	1308.2
7.5°	1327.1
10°	1345.2
12.5°	1335.8
15°	1301.1
17.5°	1246.0
20°	1167.2
22.5°	1058.6
25°	916.0
27.5°	734.8
30°	531.6
32.5°	326.1
35°	174.1
37.5°	88.2
40°	46.5
42.5°	29.9
45°	20.5
47.5°	14.2
50°	7.9
52.5°	4.7
55°	3.2
57.5°	3.2
60°	3.2
62.5°	2.4
65°	2.4
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)