

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257166

Luminaire Tested: P3AS09R659040DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257166  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R659040DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 939.0 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257166  
CATALOG NUMBER: P3AS09R659040DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1257166  
 CATALOG NUMBER: P3AS09R659040DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77				77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	251603
5°	233634
10°	225937
15°	217731
20°	201291
25°	183398
30°	141693
35°	82128
40°	32604
45°	13893
50°	3275
55°	459
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13893 cd/sqm



TEST NUMBER: P1257166  
 CATALOG NUMBER: P3AS09R659040DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.1	10.7
10°-20°	267.2	28.5
20°-30°	338.2	36.0
30°-40°	192.6	20.5
40°-50°	38.3	4.1
50°-60°	2.0	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.6	75.1
0°-40°	898.2	95.7
0°-60°	938.4	99.9
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1147	
5°	1061	100
15°	959	267
25°	758	338
35°	307	193
45°	45	38
55°	1	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1257166  
CATALOG NUMBER: P3AS09R659040DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1147.4
1°	1138.9
2°	1120.4
3°	1098.8
4°	1077.6
5°	1061.4
6°	1049.4
7°	1039.8
8°	1031.3
9°	1022.8
10°	1014.7
11°	1005.8
12°	996.5
13°	985.3
14°	973.4
15°	959.1
16°	942.1
17°	923.6
18°	903.5
19°	882.3
20°	862.6
21°	842.5
22°	824.4
23°	805.5
24°	783.5
25°	758.0
26°	727.5
27°	690.9
28°	649.6
29°	605.6
30°	559.6
31°	509.1
32°	458.9
32.5°	433.0
33°	408.0
34°	357.0
35°	306.8
36°	260.5
37°	214.6
37.5°	191.0
38°	172.1
39°	139.3
40°	113.9
42.5°	70.2
45°	44.8



TEST NUMBER: P1257166  
CATALOG NUMBER: P3AS09R659040DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	26.2
50°	9.6
52.5°	1.9
55°	1.2
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)