

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256558

Luminaire Tested: P3AS05R259040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 728.1 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256558

CATALOG NUMBER: P3AS05R259040DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256558

CATALOG NUMBER: P3AS05R259040DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	797305
5°	738585
10°	571443
15°	272941
20°	89981
25°	37938
30°	14711
35°	6371
40°	2118
45°	992
50°	375
55°	191
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 992 cd/sqm

TEST NUMBER: P1256558

CATALOG NUMBER: P3AS05R259040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.9	40.5
10°-20°	335.4	46.1
20°-30°	78.0	10.7
30°-40°	16.4	2.2
40°-50°	2.7	0.4
50°-60°	0.4	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	708.3	97.3
0°-40°	724.7	99.5
0°-60°	727.8	100.0
0°-90°	728.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3636	
5°	3355	295
15°	1202	335
25°	157	78
35°	24	16
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256558

CATALOG NUMBER: P3AS05R259040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3636.0
1°	3628.6
2°	3590.8
3°	3537.8
4°	3456.7
5°	3355.4
6°	3225.2
7°	3089.0
8°	2936.2
9°	2763.9
10°	2566.4
11°	2337.6
12°	2074.9
13°	1787.2
14°	1486.3
15°	1202.3
16°	951.0
17°	740.9
18°	582.8
19°	466.1
20°	385.6
21°	322.3
22°	270.6
23°	225.9
24°	189.0
25°	156.8
27.5°	92.9
30°	58.1
32.5°	37.2
35°	23.8
37.5°	14.3
40°	7.4
42.5°	4.8
45°	3.2
47.5°	1.8
50°	1.1
52.5°	0.5
55°	0.5
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0



TEST NUMBER: P1256558

CATALOG NUMBER: P3AS05R259040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)