

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256591

Luminaire Tested: P3AS05R309040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 280.0 lumens
Efficiency: N/A
Efficacy: 38.9 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256591
CATALOG NUMBER: P3AS05R309040DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1256591
 CATALOG NUMBER: P3AS05R309040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163386
5°	155514
10°	130815
15°	94325
20°	58525
25°	33268
30°	18484
35°	10065
40°	5296
45°	2884
50°	1535
55°	994
60°	921
65°	986
70°	833
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2884 cd/sqm



TEST NUMBER: P1256591
 CATALOG NUMBER: P3AS05R309040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.6	22.7
10°-20°	113.1	40.4
20°-30°	65.4	23.3
30°-40°	24.8	8.9
40°-50°	7.6	2.7
50°-60°	2.6	0.9
60°-70°	1.8	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.0	86.4
0°-40°	266.9	95.3
0°-60°	277.0	98.9
0°-90°	280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	280.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	745	
5°	706	64
15°	416	113
25°	138	65
35°	38	25
45°	9	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1256591
CATALOG NUMBER: P3AS05R309040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	745.1
1°	744.6
2°	740.1
3°	731.6
4°	721.0
5°	706.5
6°	688.0
7°	667.3
8°	644.3
9°	616.8
10°	587.5
11°	555.7
12°	522.1
13°	487.0
14°	451.2
15°	415.5
17.5°	327.7
20°	250.8
22.5°	185.9
25°	137.5
27.5°	100.0
30°	73.0
32.5°	52.6
35°	37.6
37.5°	26.2
40°	18.5
42.5°	13.0
45°	9.3
47.5°	6.3
50°	4.5
52.5°	3.2
55°	2.6
57.5°	2.4
60°	2.1
62.5°	1.9
65°	1.9
67.5°	1.6
70°	1.3
72.5°	1.1
75°	0.8
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.0



TEST NUMBER: P1256591
CATALOG NUMBER: P3AS05R309040DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)