

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257184

Luminaire Tested: P3AS09R659040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 790.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257184

CATALOG NUMBER: P3AS09R659040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257184

CATALOG NUMBER: P3AS09R659040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186301
5°	184063
10°	177084
15°	165881
20°	149206
25°	126685
30°	99079
35°	70617
40°	46201
45°	28561
50°	14498
55°	5123
60°	4473
65°	4514
70°	4039
75°	3982
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28561 cd/sqm

TEST NUMBER: P1257184

CATALOG NUMBER: P3AS09R659040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	9.9
10°-20°	203.4	25.7
20°-30°	237.7	30.1
30°-40°	166.1	21.0
40°-50°	73.1	9.3
50°-60°	16.3	2.1
60°-70°	8.3	1.0
70°-80°	5.0	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.5	65.8
0°-40°	685.6	86.8
0°-60°	775.0	98.1
0°-90°	790.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	790.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	850	
5°	836	79
15°	731	203
25°	524	238
35°	264	166
45°	92	73
55°	13	16
65°	9	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1257184

CATALOG NUMBER: P3AS09R659040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	849.6
2.5°	846.5
5°	836.2
7.5°	818.9
10°	795.3
12.5°	766.2
15°	730.7
17.5°	687.4
20°	639.4
22.5°	585.0
25°	523.6
27.5°	459.1
30°	391.3
32.5°	326.0
35°	263.8
37.5°	209.5
40°	161.4
42.5°	122.0
45°	92.1
47.5°	67.7
50°	42.5
52.5°	22.0
55°	13.4
57.5°	11.8
60°	10.2
62.5°	9.4
65°	8.7
67.5°	7.1
70°	6.3
72.5°	5.5
75°	4.7
77.5°	3.9
80°	3.1
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)