

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257261

Luminaire Tested: P3AS13R129040DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129040DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 964.0 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257261

CATALOG NUMBER: P3AS13R129040DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257261

CATALOG NUMBER: P3AS13R129040DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91		
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87		
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83		
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80		
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77		
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74		
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69		
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	823509
5°	730991
10°	507650
15°	300206
20°	170978
25°	97748
30°	54084
35°	28830
40°	15944
45°	8652
50°	5390
55°	4244
60°	3684
65°	3373
70°	2949
75°	3135
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8652 cd/sqm

TEST NUMBER: P1257261

CATALOG NUMBER: P3AS13R129040DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.4	29.3
10°-20°	372.7	38.7
20°-30°	191.9	19.9
30°-40°	72.1	7.5
40°-50°	23.6	2.4
50°-60°	10.1	1.1
60°-70°	6.4	0.7
70°-80°	3.8	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	847.0	87.9
0°-40°	919.1	95.3
0°-60°	952.8	98.8
0°-90°	964.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	964.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3756	
5°	3321	282
15°	1322	373
25°	404	192
35°	108	72
45°	28	24
55°	11	10
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1257261

CATALOG NUMBER: P3AS13R129040DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3755.5
1°	3748.1
2°	3698.9
3°	3605.1
4°	3481.5
5°	3320.9
6°	3138.9
7°	2939.2
8°	2717.3
9°	2498.1
10°	2279.9
12.5°	1754.2
15°	1322.4
17.5°	990.0
20°	732.7
22.5°	547.0
25°	404.0
27.5°	294.4
30°	213.6
32.5°	151.4
35°	107.7
37.5°	77.1
40°	55.7
42.5°	39.9
45°	27.9
47.5°	20.4
50°	15.8
52.5°	13.0
55°	11.1
57.5°	9.3
60°	8.4
62.5°	7.4
65°	6.5
67.5°	5.6
70°	4.6
72.5°	4.6
75°	3.7
77.5°	2.8
80°	1.9
82.5°	1.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)