

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256629

Luminaire Tested: P3AS05R359040DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359040DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 436.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256629
CATALOG NUMBER: P3AS05R359040DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1256629
 CATALOG NUMBER: P3AS05R359040DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.2	9.5
10°-20°	100.5	23.0
20°-30°	115.1	26.4
30°-40°	93.9	21.5
40°-50°	47.4	10.9
50°-60°	17.6	4.0
60°-70°	11.8	2.7
70°-80°	6.5	1.5
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.8	58.9
0°-40°	350.7	80.4
0°-60°	415.7	95.3
0°-90°	436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	454	
5°	443	41
15°	361	100
25°	251	115
35°	151	94
45°	60	47
55°	18	18
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1256629
CATALOG NUMBER: P3AS05R359040DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	454.2
1°	453.7
2°	452.6
3°	450.4
4°	447.2
5°	442.9
6°	437.5
7°	432.1
8°	425.1
9°	418.1
10°	410.0
11°	401.4
12°	392.2
13°	382.0
14°	371.2
15°	361.0
17.5°	333.5
20°	305.5
22.5°	276.9
25°	251.1
27.5°	225.7
30°	201.0
32.5°	176.2
35°	151.4
37.5°	126.6
40°	102.4
42.5°	79.7
45°	59.8
47.5°	43.1
50°	29.6
52.5°	21.6
55°	18.3
57.5°	16.7
60°	15.1
62.5°	13.5
65°	11.9
67.5°	10.2
70°	9.2
72.5°	7.5
75°	5.9
77.5°	4.8
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1



TEST NUMBER: P1256629
CATALOG NUMBER: P3AS05R359040DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)