

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257283

Luminaire Tested: P3AS13R159040DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159040DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1352.0 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257283

CATALOG NUMBER: P3AS13R159040DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257283

CATALOG NUMBER: P3AS13R159040DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	105		104	103	102		101
2	112	109	107	105	110	108	105	103	105	103	101		102	100	99		99
3	110	106	102	100	108	104	102	99	102	100	98		100	98	96		98
4	107	102	99	96	106	101	98	96	99	97	95		98	96	94		96
5	105	100	96	94	103	99	96	93	97	94	92		96	93	92		94
6	102	97	94	91	101	96	93	91	95	92	90		94	92	90		93
7	100	95	91	89	99	94	91	89	93	90	88		92	90	88		91
8	98	93	89	87	97	92	89	87	91	89	87		91	88	86		90
9	96	91	88	85	96	91	87	85	90	87	85		89	87	85		89
10	95	89	86	84	94	89	86	84	88	85	83		88	85	83		87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2574552
5°	2099378
10°	1028148
15°	314690
20°	133268
25°	60294
30°	23497
35°	10842
40°	3378
45°	1271
50°	512
55°	191
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1271 cd/sqm

TEST NUMBER: P1257283

CATALOG NUMBER: P3AS13R159040DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	742.4	54.9
10°-20°	455.5	33.7
20°-30°	122.4	9.1
30°-40°	27.0	2.0
40°-50°	3.8	0.3
50°-60°	0.7	0.0
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1320.3	97.7
0°-40°	1347.2	99.6
0°-60°	1351.7	100.0
0°-90°	1352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1352.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11741	
5°	9538	742
15°	1386	456
25°	249	122
35°	40	27
45°	4	4
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1257283

CATALOG NUMBER: P3AS13R159040DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11740.9
1°	11667.6
2°	11432.3
3°	11008.3
4°	10370.1
5°	9537.5
6°	8595.8
7°	7546.9
8°	6583.1
9°	5561.3
10°	4617.5
11°	3683.5
12°	2834.0
13°	2179.8
14°	1725.6
15°	1386.2
17.5°	859.2
20°	571.1
22.5°	384.5
25°	249.2
27.5°	147.6
30°	92.8
32.5°	62.5
35°	40.5
37.5°	22.6
40°	11.8
42.5°	6.7
45°	4.1
47.5°	2.6
50°	1.5
52.5°	1.0
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1257283

CATALOG NUMBER: P3AS13R159040DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)