

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256734

Luminaire Tested: P3AS05R559040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256734

CATALOG NUMBER: P3AS05R559040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256734

CATALOG NUMBER: P3AS05R559040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79073
5°	78274
10°	75594
15°	69876
20°	60299
25°	47616
30°	33777
35°	21790
40°	13082
45°	7381
50°	3957
55°	1415
60°	1272
65°	1245
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7381 cd/sqm

TEST NUMBER: P1256734

CATALOG NUMBER: P3AS05R559040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.4	11.6
10°-20°	85.1	29.6
20°-30°	89.2	31.0
30°-40°	52.0	18.1
40°-50°	19.5	6.8
50°-60°	4.6	1.6
60°-70°	2.3	0.8
70°-80°	1.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.7	72.1
0°-40°	259.8	90.2
0°-60°	283.9	98.6
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	361	
5°	356	33
15°	308	85
25°	197	89
35°	81	52
45°	24	19
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256734

CATALOG NUMBER: P3AS05R559040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	360.6
2.5°	359.6
5°	355.6
7.5°	349.3
10°	339.5
12.5°	325.8
15°	307.8
17.5°	285.1
20°	258.4
22.5°	228.5
25°	196.8
27.5°	164.3
30°	133.4
32.5°	105.4
35°	81.4
37.5°	61.8
40°	45.7
42.5°	32.8
45°	23.8
47.5°	17.2
50°	11.6
52.5°	6.6
55°	3.7
57.5°	3.2
60°	2.9
62.5°	2.6
65°	2.4
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.3
77.5°	1.1
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)