

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257364

Luminaire Tested: P3AS13R309040DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309040DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1330.9 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257364

CATALOG NUMBER: P3AS13R309040DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1257364

CATALOG NUMBER: P3AS13R309040DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95
4	105	100	96	93	103	99	95	92	97	94	91		95	92	90		93
5	102	96	92	89	100	95	92	89	94	90	88		92	89	87		91
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		89
7	96	90	86	83	95	89	86	83	88	85	83		87	84	82		86
8	94	87	83	81	93	87	83	80	86	83	80		85	82	80		84
9	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82
10	89	83	79	76	88	82	78	76	82	78	76		81	78	76		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1083882
5°	1063391
10°	941376
15°	596417
20°	226400
25°	67020
30°	26460
35°	8111
40°	3578
45°	1302
50°	1058
55°	803
60°	921
65°	1090
70°	641
75°	847
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1302 cd/sqm

TEST NUMBER: P1257364

CATALOG NUMBER: P3AS13R309040DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.1	33.4
10°-20°	692.1	52.0
20°-30°	160.7	12.1
30°-40°	24.9	1.9
40°-50°	4.2	0.3
50°-60°	2.0	0.1
60°-70°	1.7	0.1
70°-80°	1.1	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1296.9	97.4
0°-40°	1321.8	99.3
0°-60°	1328.0	99.8
0°-90°	1330.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4943	
5°	4831	444
15°	2627	692
25°	277	161
35°	30	25
45°	4	4
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1257364

CATALOG NUMBER: P3AS13R309040DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4942.9
1°	4939.8
2°	4926.2
3°	4903.2
4°	4873.9
5°	4831.0
6°	4777.7
7°	4698.3
8°	4589.5
9°	4429.6
10°	4227.8
11°	3967.5
12°	3673.7
13°	3347.5
14°	2988.9
15°	2627.2
17.5°	1718.7
20°	970.2
22.5°	495.5
25°	277.0
27.5°	170.4
30°	104.5
32.5°	56.5
35°	30.3
37.5°	19.9
40°	12.5
42.5°	7.3
45°	4.2
47.5°	3.1
50°	3.1
52.5°	2.1
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	2.1
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1257364
CATALOG NUMBER: P3AS13R309040DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)