

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256745

Luminaire Tested: P3AS05R559040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 456.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256745

CATALOG NUMBER: P3AS05R559040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256745

CATALOG NUMBER: P3AS05R559040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85739
5°	84635
10°	81317
15°	76050
20°	69376
25°	61891
30°	54135
35°	44972
40°	35466
45°	24065
50°	14703
55°	7608
60°	7105
65°	6693
70°	6219
75°	5507
80°	5430
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24065 cd/sqm

TEST NUMBER: P1256745

CATALOG NUMBER: P3AS05R559040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.1	7.9
10°-20°	93.6	20.5
20°-30°	117.2	25.7
30°-40°	104.7	23.0
40°-50°	61.3	13.4
50°-60°	21.2	4.6
60°-70°	12.8	2.8
70°-80°	7.1	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.9	54.2
0°-40°	351.6	77.1
0°-60°	434.1	95.2
0°-90°	456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	456.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	391	
5°	384	36
15°	335	94
25°	256	117
35°	168	105
45°	78	61
55°	20	21
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1256745

CATALOG NUMBER: P3AS05R559040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	391.0
2.5°	388.9
5°	384.5
7.5°	375.9
10°	365.2
12.5°	351.7
15°	335.0
17.5°	317.2
20°	297.3
22.5°	276.8
25°	255.8
27.5°	234.8
30°	213.8
32.5°	191.2
35°	168.0
37.5°	145.4
40°	123.9
42.5°	100.7
45°	77.6
47.5°	59.2
50°	43.1
52.5°	28.0
55°	19.9
57.5°	17.8
60°	16.2
62.5°	14.5
65°	12.9
67.5°	11.3
70°	9.7
72.5°	8.1
75°	6.5
77.5°	5.4
80°	4.3
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)