

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256763

Luminaire Tested: P3AS05R609040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 278.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256763

CATALOG NUMBER: P3AS05R609040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256763

CATALOG NUMBER: P3AS05R609040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65653
5°	65023
10°	63125
15°	59138
20°	52341
25°	43793
30°	34309
35°	24895
40°	16574
45°	10327
50°	5595
55°	1606
60°	1491
65°	1349
70°	1346
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10327 cd/sqm

TEST NUMBER: P1256763

CATALOG NUMBER: P3AS05R609040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.8	10.0
10°-20°	72.3	26.0
20°-30°	82.4	29.6
30°-40°	58.4	21.0
40°-50°	26.5	9.5
50°-60°	5.6	2.0
60°-70°	2.7	1.0
70°-80°	1.7	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.5	65.6
0°-40°	240.9	86.7
0°-60°	273.0	98.2
0°-90°	278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	299	
5°	295	28
15°	260	72
25°	181	82
35°	93	58
45°	33	27
55°	4	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1256763

CATALOG NUMBER: P3AS05R609040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	299.4
2.5°	298.3
5°	295.4
7.5°	290.4
10°	283.5
12.5°	273.7
15°	260.5
17.5°	243.9
20°	224.3
22.5°	203.2
25°	181.0
27.5°	158.3
30°	135.5
32.5°	113.9
35°	93.0
37.5°	74.5
40°	57.9
42.5°	43.9
45°	33.3
47.5°	24.8
50°	16.4
52.5°	7.7
55°	4.2
57.5°	3.7
60°	3.4
62.5°	3.2
65°	2.6
67.5°	2.4
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)