

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257383

Luminaire Tested: P3AS13R309040DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309040DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257383
CATALOG NUMBER: P3AS13R309040DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1257383
 CATALOG NUMBER: P3AS13R309040DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201278
5°	196764
10°	182985
15°	162816
20°	140036
25°	118628
30°	98471
35°	77256
40°	55361
45°	36314
50°	20673
55°	13572
60°	12850
65°	11934
70°	10707
75°	9743
80°	9218
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36314 cd/sqm



TEST NUMBER: P1257383
 CATALOG NUMBER: P3AS13R309040DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	9.7
10°-20°	199.4	23.4
20°-30°	224.7	26.4
30°-40°	179.4	21.1
40°-50°	92.2	10.8
50°-60°	34.7	4.1
60°-70°	22.8	2.7
70°-80°	12.3	1.4
80°-90°	3.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.1	59.5
0°-40°	686.5	80.6
0°-60°	813.4	95.5
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	918	
5°	894	83
15°	717	199
25°	490	225
35°	289	179
45°	117	92
55°	36	35
65°	23	23
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P1257383
CATALOG NUMBER: P3AS13R309040DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	917.9
1°	917.9
2°	914.8
3°	909.6
4°	902.3
5°	893.9
6°	883.4
7°	869.8
8°	855.2
9°	838.5
10°	821.8
11°	802.9
12°	783.1
13°	762.2
14°	740.2
15°	717.2
17.5°	658.7
20°	600.1
22.5°	543.7
25°	490.3
27.5°	438.1
30°	388.9
32.5°	338.7
35°	288.6
37.5°	239.4
40°	193.4
42.5°	152.6
45°	117.1
47.5°	86.8
50°	60.6
52.5°	42.9
55°	35.5
57.5°	32.4
60°	29.3
62.5°	26.1
65°	23.0
67.5°	19.9
70°	16.7
72.5°	13.6
75°	11.5
77.5°	9.4
80°	7.3
82.5°	5.2
85°	3.1
87.5°	1.0



TEST NUMBER: P1257383
CATALOG NUMBER: P3AS13R309040DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)