

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256764

Luminaire Tested: P3AS05R609040DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609040DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 567.0 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256764

CATALOG NUMBER: P3AS05R609040DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1256764

CATALOG NUMBER: P3AS05R609040DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	70	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133893
5°	132621
10°	128744
15°	120636
20°	106759
25°	89304
30°	70011
35°	50781
40°	33778
45°	21056
50°	11394
55°	3288
60°	3070
65°	2802
70°	2757
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21056 cd/sqm

TEST NUMBER: P1256764

CATALOG NUMBER: P3AS05R609040DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.7	10.0
10°-20°	147.4	26.0
20°-30°	168.0	29.6
30°-40°	119.2	21.0
40°-50°	54.1	9.5
50°-60°	11.4	2.0
60°-70°	5.6	1.0
70°-80°	3.4	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	372.2	65.6
0°-40°	491.4	86.7
0°-60°	556.9	98.2
0°-90°	567.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	567.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	611	
5°	602	57
15°	531	147
25°	369	168
35°	190	119
45°	68	54
55°	9	11
65°	5	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256764

CATALOG NUMBER: P3AS05R609040DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	610.6
2.5°	608.4
5°	602.5
7.5°	592.3
10°	578.2
12.5°	558.3
15°	531.4
17.5°	497.4
20°	457.5
22.5°	414.4
25°	369.1
27.5°	322.8
30°	276.5
32.5°	232.3
35°	189.7
37.5°	152.0
40°	118.0
42.5°	89.5
45°	67.9
47.5°	50.7
50°	33.4
52.5°	15.6
55°	8.6
57.5°	7.5
60°	7.0
62.5°	6.5
65°	5.4
67.5°	4.9
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)