

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257394

Luminaire Tested: P3AS13R309040DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1257394  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309040DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 588.0 lumens  
Efficiency: N/A  
Efficacy: 40.3 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257394  
CATALOG NUMBER: P3AS13R309040DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1257394  
 CATALOG NUMBER: P3AS13R309040DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	58	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	190906
5°	180013
10°	153883
15°	123315
20°	96118
25°	72294
30°	52717
35°	37156
40°	25476
45°	18234
50°	14942
55°	14413
60°	14560
65°	14891
70°	15451
75°	16606
80°	17174
85°	18870

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 20328 cd/sqm



TEST NUMBER: P1257394  
 CATALOG NUMBER: P3AS13R309040DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.0	12.6
10°-20°	150.9	25.7
20°-30°	137.5	23.4
30°-40°	87.5	14.9
40°-50°	46.8	8.0
50°-60°	34.3	5.8
60°-70°	28.8	4.9
70°-80°	20.1	3.4
80°-90°	8.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.5	61.6
0°-40°	450.0	76.5
0°-60°	531.1	90.3
0°-90°	588.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	588.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	871	
5°	818	74
15°	543	151
25°	299	138
35°	139	88
45°	59	47
55°	38	34
65°	29	29
75°	20	20
85°	8	8
90°	0	



TEST NUMBER: P1257394  
CATALOG NUMBER: P3AS13R309040DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	870.6
2.5°	857.0
5°	817.8
7.5°	760.5
10°	691.1
12.5°	617.1
15°	543.2
17.5°	475.3
20°	411.9
22.5°	353.1
25°	298.8
27.5°	250.5
30°	208.2
32.5°	169.0
35°	138.8
37.5°	110.1
40°	89.0
42.5°	70.9
45°	58.8
47.5°	48.3
50°	43.8
52.5°	40.7
55°	37.7
57.5°	36.2
60°	33.2
62.5°	31.7
65°	28.7
67.5°	27.2
70°	24.1
72.5°	21.1
75°	19.6
77.5°	16.6
80°	13.6
82.5°	12.1
85°	7.5
87.5°	3.0
90°	0.0

(END OF REPORT)