

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256774

Luminaire Tested: P3AS05R609040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 444.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256774

CATALOG NUMBER: P3AS05R609040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256774

CATALOG NUMBER: P3AS05R609040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78809
5°	77922
10°	75238
15°	71079
20°	65526
25°	59326
30°	52666
35°	44999
40°	35781
45°	25243
50°	15078
55°	7608
60°	7324
65°	6693
70°	6219
75°	5931
80°	5430
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25243 cd/sqm

TEST NUMBER: P1256774

CATALOG NUMBER: P3AS05R609040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	7.5
10°-20°	87.5	19.7
20°-30°	112.4	25.3
30°-40°	104.1	23.5
40°-50°	63.4	14.3
50°-60°	21.1	4.8
60°-70°	12.8	2.9
70°-80°	7.3	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.1	52.5
0°-40°	337.3	76.0
0°-60°	421.8	95.0
0°-90°	444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	359	
5°	354	33
15°	313	88
25°	245	112
35°	168	104
45°	81	63
55°	20	21
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1256774

CATALOG NUMBER: P3AS05R609040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	359.4
2.5°	357.8
5°	354.0
7.5°	347.0
10°	337.9
12.5°	326.6
15°	313.1
17.5°	297.5
20°	280.8
22.5°	263.0
25°	245.2
27.5°	226.9
30°	208.0
32.5°	189.1
35°	168.1
37.5°	146.0
40°	125.0
42.5°	102.9
45°	81.4
47.5°	63.0
50°	44.2
52.5°	26.4
55°	19.9
57.5°	18.3
60°	16.7
62.5°	14.5
65°	12.9
67.5°	11.3
70°	9.7
72.5°	8.1
75°	7.0
77.5°	5.4
80°	4.3
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)