

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256780

Luminaire Tested: P3AS05R609040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 392.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256780

CATALOG NUMBER: P3AS05R609040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256780

CATALOG NUMBER: P3AS05R609040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		58
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99334
5°	97116
10°	90913
15°	81567
20°	70146
25°	57995
30°	45830
35°	34024
40°	23444
45°	14699
50°	8085
55°	4741
60°	4254
65°	3632
70°	3077
75°	3219
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14699 cd/sqm

TEST NUMBER: P1256780

CATALOG NUMBER: P3AS05R609040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	10.5
10°-20°	99.8	25.5
20°-30°	109.5	27.9
30°-40°	79.7	20.3
40°-50°	37.7	9.6
50°-60°	12.3	3.1
60°-70°	7.0	1.8
70°-80°	3.8	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.3	63.9
0°-40°	330.1	84.2
0°-60°	380.1	97.0
0°-90°	392.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	392.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	441	41
15°	359	100
25°	240	109
35°	127	80
45°	47	38
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1256780

CATALOG NUMBER: P3AS05R609040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	453.0
2.5°	450.4
5°	441.2
7.5°	427.2
10°	408.3
12.5°	385.7
15°	359.3
17.5°	330.8
20°	300.6
22.5°	269.9
25°	239.7
27.5°	209.6
30°	181.0
32.5°	153.5
35°	127.1
37.5°	103.4
40°	81.9
42.5°	63.0
45°	47.4
47.5°	34.5
50°	23.7
52.5°	15.6
55°	12.4
57.5°	10.8
60°	9.7
62.5°	8.1
65°	7.0
67.5°	5.9
70°	4.8
72.5°	4.3
75°	3.8
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)