

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256797

Luminaire Tested: P3AS05R659040DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659040DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 540.0 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256797

CATALOG NUMBER: P3AS05R659040DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256797

CATALOG NUMBER: P3AS05R659040DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		58
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127358
5°	125820
10°	121040
15°	113395
20°	101976
25°	86594
30°	67732
35°	48265
40°	31573
45°	19537
50°	9927
55°	3479
60°	3070
65°	3061
70°	2757
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 19537 cd/sqm

TEST NUMBER: P1256797

CATALOG NUMBER: P3AS05R659040DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	9.9
10°-20°	139.0	25.7
20°-30°	162.5	30.1
30°-40°	113.5	21.0
40°-50°	50.0	9.3
50°-60°	11.1	2.1
60°-70°	5.7	1.0
70°-80°	3.4	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.1	65.8
0°-40°	468.7	86.8
0°-60°	529.8	98.1
0°-90°	540.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	572	54
15°	500	139
25°	358	162
35°	180	114
45°	63	50
55°	9	11
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256797

CATALOG NUMBER: P3AS05R659040DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	580.8
2.5°	578.6
5°	571.6
7.5°	559.8
10°	543.6
12.5°	523.7
15°	499.5
17.5°	469.9
20°	437.0
22.5°	399.9
25°	357.9
27.5°	313.8
30°	267.5
32.5°	222.8
35°	180.3
37.5°	143.2
40°	110.3
42.5°	83.4
45°	63.0
47.5°	46.3
50°	29.1
52.5°	15.1
55°	9.1
57.5°	8.1
60°	7.0
62.5°	6.5
65°	5.9
67.5°	4.8
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)