

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257440

Luminaire Tested: P3AS13R409040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 458.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257440

CATALOG NUMBER: P3AS13R409040DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257440

CATALOG NUMBER: P3AS13R409040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102821
5°	100946
10°	95166
15°	86425
20°	75933
25°	64842
30°	53704
35°	41412
40°	29484
45°	19878
50°	10848
55°	7646
60°	7192
65°	6641
70°	5898
75°	5676
80°	4546
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19878 cd/sqm

TEST NUMBER: P1257440

CATALOG NUMBER: P3AS13R409040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	9.3
10°-20°	106.1	23.2
20°-30°	122.6	26.8
30°-40°	96.6	21.1
40°-50°	49.6	10.8
50°-60°	19.0	4.1
60°-70°	12.5	2.7
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.4	59.3
0°-40°	368.1	80.4
0°-60°	436.6	95.3
0°-90°	458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	469	
5°	459	43
15°	381	106
25°	268	123
35°	155	97
45°	64	50
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1257440

CATALOG NUMBER: P3AS13R409040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	468.9
2.5°	466.3
5°	458.6
7.5°	445.3
10°	427.4
12.5°	406.3
15°	380.7
17.5°	354.1
20°	325.4
22.5°	296.2
25°	268.0
27.5°	239.8
30°	212.1
32.5°	184.0
35°	154.7
37.5°	127.6
40°	103.0
42.5°	82.0
45°	64.1
47.5°	46.6
50°	31.8
52.5°	23.1
55°	20.0
57.5°	17.9
60°	16.4
62.5°	14.3
65°	12.8
67.5°	10.8
70°	9.2
72.5°	7.7
75°	6.7
77.5°	5.1
80°	3.6
82.5°	3.1
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)