

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256821

Luminaire Tested: P3AS05R709040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 266.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256821

CATALOG NUMBER: P3AS05R709040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256821

CATALOG NUMBER: P3AS05R709040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51487
5°	50869
10°	49409
15°	47310
20°	44314
25°	40260
30°	34790
35°	27733
40°	20181
45°	13273
50°	6209
55°	1912
60°	1842
65°	1764
70°	1667
75°	1779
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13273 cd/sqm

TEST NUMBER: P1256821

CATALOG NUMBER: P3AS05R709040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.8	8.2
10°-20°	58.3	21.9
20°-30°	75.8	28.5
30°-40°	64.3	24.2
40°-50°	33.2	12.5
50°-60°	6.4	2.4
60°-70°	3.5	1.3
70°-80°	2.1	0.8
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.9	58.6
0°-40°	220.2	82.8
0°-60°	259.8	97.7
0°-90°	266.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	266.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	235	
5°	231	22
15°	208	58
25°	166	76
35°	104	64
45°	43	33
55°	5	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1256821

CATALOG NUMBER: P3AS05R709040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	234.8
2.5°	234.0
5°	231.1
7.5°	226.9
10°	221.9
12.5°	215.6
15°	208.4
17.5°	199.7
20°	189.9
22.5°	178.8
25°	166.4
27.5°	152.4
30°	137.4
32.5°	120.7
35°	103.6
37.5°	86.6
40°	70.5
42.5°	55.5
45°	42.8
47.5°	31.4
50°	18.2
52.5°	7.9
55°	5.0
57.5°	4.8
60°	4.2
62.5°	4.0
65°	3.4
67.5°	3.2
70°	2.6
72.5°	2.4
75°	2.1
77.5°	1.6
80°	1.3
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)