

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257449

Luminaire Tested: P3AS13R409040DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1257449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R409040DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 768.0 lumens  
Efficiency: N/A  
Efficacy: 52.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1257449

CATALOG NUMBER: P3AS13R409040DE010 E3DLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1257449

CATALOG NUMBER: P3AS13R409040DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 93  | 97  | 94  | 91  |  | 94  | 92  | 89  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 86  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 63  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 239148 |
| 5°  | 234294 |
| 10° | 218143 |
| 15° | 190126 |
| 20° | 153220 |
| 25° | 114853 |
| 30° | 80747  |
| 35° | 52896  |
| 40° | 32031  |
| 45° | 19134  |
| 50° | 11428  |
| 55° | 9175   |
| 60° | 8245   |
| 65° | 7057   |
| 70° | 6732   |
| 75° | 5338   |
| 80° | 5304   |
| 85° | 5284   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19134 cd/sqm

TEST NUMBER: P1257449

CATALOG NUMBER: P3AS13R409040DE010 E3DLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 98.8   | 12.9      |
| 10°-20°   | 230.7  | 30.0      |
| 20°-30°   | 217.4  | 28.3      |
| 30°-40°   | 125.7  | 16.4      |
| 40°-50°   | 50.1   | 6.5       |
| 50°-60°   | 22.2   | 2.9       |
| 60°-70°   | 13.7   | 1.8       |
| 70°-80°   | 7.2    | 0.9       |
| 80°-90°   | 2.3    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 546.9  | 71.2      |
| 0°-40°    | 672.6  | 87.6      |
| 0°-60°    | 744.9  | 97.0      |
| 0°-90°    | 768.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 768.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1091 |      |
| 5°  | 1064 | 99   |
| 15° | 838  | 231  |
| 25° | 475  | 217  |
| 35° | 198  | 126  |
| 45° | 62   | 50   |
| 55° | 24   | 22   |
| 65° | 14   | 14   |
| 75° | 6    | 7    |
| 85° | 2    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1257449

CATALOG NUMBER: P3AS13R409040DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1090.6 |
| 2.5°  | 1084.3 |
| 5°    | 1064.4 |
| 7.5°  | 1027.8 |
| 10°   | 979.7  |
| 12.5° | 914.9  |
| 15°   | 837.5  |
| 17.5° | 750.7  |
| 20°   | 656.6  |
| 22.5° | 562.5  |
| 25°   | 474.7  |
| 27.5° | 393.1  |
| 30°   | 318.9  |
| 32.5° | 254.1  |
| 35°   | 197.6  |
| 37.5° | 149.5  |
| 40°   | 111.9  |
| 42.5° | 83.6   |
| 45°   | 61.7   |
| 47.5° | 45.0   |
| 50°   | 33.5   |
| 52.5° | 27.2   |
| 55°   | 24.0   |
| 57.5° | 22.0   |
| 60°   | 18.8   |
| 62.5° | 15.7   |
| 65°   | 13.6   |
| 67.5° | 11.5   |
| 70°   | 10.5   |
| 72.5° | 8.4    |
| 75°   | 6.3    |
| 77.5° | 5.2    |
| 80°   | 4.2    |
| 82.5° | 3.1    |
| 85°   | 2.1    |
| 87.5° | 1.0    |
| 90°   | 0.0    |

(END OF REPORT)