

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256877

Luminaire Tested: P3AS09R159040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 400.1 lumens
Efficiency: N/A
Efficacy: 36.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256877

CATALOG NUMBER: P3AS09R159040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256877

CATALOG NUMBER: P3AS09R159040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	341705
5°	303323
10°	210640
15°	124564
20°	70940
25°	40551
30°	22434
35°	11966
40°	6612
45°	3597
50°	2252
55°	1759
60°	1535
65°	1401
70°	1218
75°	1271
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3597 cd/sqm

TEST NUMBER: P1256877

CATALOG NUMBER: P3AS09R159040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	29.3
10°-20°	154.6	38.7
20°-30°	79.6	19.9
30°-40°	29.9	7.5
40°-50°	9.8	2.5
50°-60°	4.2	1.1
60°-70°	2.7	0.7
70°-80°	1.6	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.5	87.9
0°-40°	381.3	95.3
0°-60°	395.4	98.8
0°-90°	400.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	400.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1558	
5°	1378	117
15°	549	155
25°	168	80
35°	45	30
45°	12	10
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1256877

CATALOG NUMBER: P3AS09R159040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1558.3
1°	1555.2
2°	1534.8
3°	1495.9
4°	1444.6
5°	1378.0
6°	1302.4
7°	1219.6
8°	1127.5
9°	1036.6
10°	946.0
12.5°	727.9
15°	548.7
17.5°	410.8
20°	304.0
22.5°	227.0
25°	167.6
27.5°	122.2
30°	88.6
32.5°	62.8
35°	44.7
37.5°	32.0
40°	23.1
42.5°	16.6
45°	11.6
47.5°	8.5
50°	6.6
52.5°	5.4
55°	4.6
57.5°	3.9
60°	3.5
62.5°	3.1
65°	2.7
67.5°	2.3
70°	1.9
72.5°	1.9
75°	1.5
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)