

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257476

Luminaire Tested: P3AS13R459040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 754.0 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257476

CATALOG NUMBER: P3AS13R459040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1257476

CATALOG NUMBER: P3AS13R459040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224587
5°	219458
10°	202446
15°	176051
20°	144609
25°	112531
30°	83101
35°	58464
40°	36497
45°	19785
50°	10712
55°	9175
60°	8245
65°	7057
70°	6027
75°	6185
80°	5304
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 19785 cd/sqm

TEST NUMBER: P1257476

CATALOG NUMBER: P3AS13R459040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.3	12.2
10°-20°	214.4	28.4
20°-30°	212.8	28.2
30°-40°	137.1	18.2
40°-50°	52.8	7.0
50°-60°	21.5	2.8
60°-70°	13.6	1.8
70°-80°	7.3	1.0
80°-90°	2.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.5	68.9
0°-40°	656.6	87.1
0°-60°	730.9	96.9
0°-90°	754.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	754.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1024	
5°	997	92
15°	776	214
25°	465	213
35°	218	137
45°	64	53
55°	24	21
65°	14	14
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1257476

CATALOG NUMBER: P3AS13R459040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1024.2
2.5°	1019.0
5°	997.0
7.5°	959.4
10°	909.2
12.5°	846.5
15°	775.5
17.5°	698.1
20°	619.7
22.5°	540.3
25°	465.1
27.5°	394.0
30°	328.2
32.5°	270.7
35°	218.4
37.5°	171.4
40°	127.5
42.5°	92.0
45°	63.8
47.5°	42.8
50°	31.4
52.5°	26.1
55°	24.0
57.5°	20.9
60°	18.8
62.5°	15.7
65°	13.6
67.5°	11.5
70°	9.4
72.5°	8.4
75°	7.3
77.5°	5.2
80°	4.2
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)