

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257494

Luminaire Tested: P3AS13R509040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 448.9 lumens
Efficiency: N/A
Efficacy: 30.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257494

CATALOG NUMBER: P3AS13R509040DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1257494

CATALOG NUMBER: P3AS13R509040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91243
5°	89896
10°	85926
15°	79569
20°	71500
25°	62858
30°	53451
35°	43339
40°	32575
45°	20963
50°	9961
55°	7837
60°	7412
65°	6901
70°	6219
75°	5676
80°	5177
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20963 cd/sqm

TEST NUMBER: P1257494

CATALOG NUMBER: P3AS13R509040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	8.5
10°-20°	97.7	21.8
20°-30°	118.7	26.4
30°-40°	100.7	22.4
40°-50°	52.3	11.7
50°-60°	18.8	4.2
60°-70°	13.1	2.9
70°-80°	7.1	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.7	56.7
0°-40°	355.4	79.2
0°-60°	426.6	95.0
0°-90°	448.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	448.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	416	
5°	408	38
15°	350	98
25°	260	119
35°	162	101
45°	68	52
55°	20	19
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1257494

CATALOG NUMBER: P3AS13R509040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	416.1
2.5°	414.6
5°	408.4
7.5°	399.2
10°	385.9
12.5°	369.0
15°	350.5
17.5°	329.5
20°	306.4
22.5°	282.9
25°	259.8
27.5°	235.7
30°	211.1
32.5°	186.5
35°	161.9
37.5°	137.8
40°	113.8
42.5°	90.7
45°	67.6
47.5°	45.1
50°	29.2
52.5°	22.5
55°	20.5
57.5°	18.4
60°	16.9
62.5°	14.9
65°	13.3
67.5°	11.3
70°	9.7
72.5°	8.2
75°	6.7
77.5°	5.1
80°	4.1
82.5°	3.1
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)