

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256914

Luminaire Tested: P3AS09R209040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 304.0 lumens
Efficiency: N/A
Efficacy: 27.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256914

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256914

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75191
5°	73189
10°	67333
15°	59251
20°	50824
25°	42704
30°	34512
35°	26261
40°	18692
45°	12342
50°	7642
55°	5008
60°	4561
65°	4203
70°	3975
75°	3558
80°	3410
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12342 cd/sqm

TEST NUMBER: P1256914

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.8	10.1
10°-20°	72.7	23.9
20°-30°	80.7	26.5
30°-40°	61.5	20.2
40°-50°	31.5	10.4
50°-60°	12.9	4.3
60°-70°	8.1	2.7
70°-80°	4.5	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.1	60.6
0°-40°	245.6	80.8
0°-60°	290.1	95.4
0°-90°	304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	343	
5°	332	31
15°	261	73
25°	176	81
35°	98	62
45°	40	32
55°	13	13
65°	8	8
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1256914

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	342.9
1°	343.3
2°	341.8
3°	339.8
4°	336.7
5°	332.5
6°	327.5
7°	322.1
8°	316.3
9°	309.3
10°	302.4
12.5°	282.3
15°	261.0
17.5°	239.4
20°	217.8
22.5°	196.2
25°	176.5
27.5°	156.8
30°	136.3
32.5°	117.0
35°	98.1
37.5°	81.5
40°	65.3
42.5°	51.4
45°	39.8
47.5°	30.1
50°	22.4
52.5°	16.6
55°	13.1
57.5°	12.0
60°	10.4
62.5°	9.3
65°	8.1
67.5°	7.0
70°	6.2
72.5°	5.0
75°	4.2
77.5°	3.5
80°	2.7
82.5°	1.9
85°	1.2
87.5°	0.4
90°	0.0

(END OF REPORT)