

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256919

Luminaire Tested: P3AS09R209040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 620.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256919

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256919

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153365
5°	149262
10°	137317
15°	120863
20°	103656
25°	87078
30°	70391
35°	53538
40°	38100
45°	25150
50°	15590
55°	10246
60°	9341
65°	8561
70°	8078
75°	7371
80°	6945
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25150 cd/sqm

TEST NUMBER: P1256919

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.7	10.1
10°-20°	148.2	23.9
20°-30°	164.5	26.5
30°-40°	125.5	20.2
40°-50°	64.2	10.4
50°-60°	26.4	4.3
60°-70°	16.5	2.7
70°-80°	9.2	1.5
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.5	60.6
0°-40°	501.0	80.8
0°-60°	591.6	95.4
0°-90°	620.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	699	
5°	678	63
15°	532	148
25°	360	165
35°	200	125
45°	81	64
55°	27	26
65°	16	16
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1256919

CATALOG NUMBER: P3AS09R209040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	699.4
1°	700.2
2°	697.0
3°	693.1
4°	686.8
5°	678.1
6°	667.9
7°	656.8
8°	645.0
9°	630.8
10°	616.7
12.5°	575.7
15°	532.4
17.5°	488.3
20°	444.2
22.5°	400.1
25°	359.9
27.5°	319.8
30°	278.0
32.5°	238.6
35°	200.0
37.5°	166.2
40°	133.1
42.5°	104.7
45°	81.1
47.5°	61.4
50°	45.7
52.5°	33.9
55°	26.8
57.5°	24.4
60°	21.3
62.5°	18.9
65°	16.5
67.5°	14.2
70°	12.6
72.5°	10.2
75°	8.7
77.5°	7.1
80°	5.5
82.5°	3.9
85°	2.4
87.5°	0.8
90°	0.0

(END OF REPORT)