

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257527

Luminaire Tested: P3AS13R559040DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559040DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 885.1 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257527

CATALOG NUMBER: P3AS13R559040DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1257527

CATALOG NUMBER: P3AS13R559040DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166412
5°	164274
10°	157802
15°	147606
20°	134645
25°	120128
30°	105079
35°	87294
40°	68815
45°	46672
50°	28519
55°	14795
60°	13771
65°	13023
70°	12053
75°	10590
80°	10607
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46672 cd/sqm

TEST NUMBER: P1257527

CATALOG NUMBER: P3AS13R559040DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	7.9
10°-20°	181.7	20.5
20°-30°	227.6	25.7
30°-40°	203.1	23.0
40°-50°	118.9	13.4
50°-60°	41.1	4.6
60°-70°	24.8	2.8
70°-80°	13.8	1.6
80°-90°	4.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.3	54.2
0°-40°	682.4	77.1
0°-60°	842.5	95.2
0°-90°	885.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	885.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	759	
5°	746	70
15°	650	182
25°	496	228
35°	326	203
45°	150	119
55°	39	41
65°	25	25
75°	12	14
85°	3	4
90°	0	

TEST NUMBER: P1257527

CATALOG NUMBER: P3AS13R559040DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	758.9
2.5°	754.7
5°	746.3
7.5°	729.6
10°	708.7
12.5°	682.6
15°	650.2
17.5°	615.7
20°	577.0
22.5°	537.3
25°	496.5
27.5°	455.7
30°	415.0
32.5°	371.1
35°	326.1
37.5°	282.2
40°	240.4
42.5°	195.5
45°	150.5
47.5°	115.0
50°	83.6
52.5°	54.4
55°	38.7
57.5°	34.5
60°	31.4
62.5°	28.2
65°	25.1
67.5°	22.0
70°	18.8
72.5°	15.7
75°	12.5
77.5°	10.5
80°	8.4
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

(END OF REPORT)