

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257539

Luminaire Tested: P3AS13R609040DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609040DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1351.9 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257539

CATALOG NUMBER: P3AS13R609040DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1257539

CATALOG NUMBER: P3AS13R609040DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322847
5°	310037
10°	319210
15°	323316
20°	285485
25°	240595
30°	195144
35°	127074
40°	58366
45°	22390
50°	7505
55°	1988
60°	1842
65°	1608
70°	1346
75°	1779
80°	1263
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22390 cd/sqm

TEST NUMBER: P1257539

CATALOG NUMBER: P3AS13R609040DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.6	10.0
10°-20°	390.0	28.8
20°-30°	454.9	33.6
30°-40°	293.6	21.7
40°-50°	65.8	4.9
50°-60°	6.6	0.5
60°-70°	3.1	0.2
70°-80°	1.8	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	980.5	72.5
0°-40°	1274.0	94.2
0°-60°	1346.4	99.6
0°-90°	1351.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1351.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1472	
5°	1408	136
15°	1424	390
25°	994	455
35°	475	294
45°	72	66
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1257539

CATALOG NUMBER: P3AS13R609040DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1472.3
2.5°	1448.3
5°	1408.5
7.5°	1406.4
10°	1433.6
12.5°	1451.4
15°	1424.2
17.5°	1342.6
20°	1223.4
22.5°	1099.0
25°	994.4
27.5°	892.0
30°	770.7
32.5°	628.5
35°	474.7
37.5°	324.2
40°	203.9
42.5°	122.3
45°	72.2
47.5°	41.8
50°	22.0
52.5°	7.3
55°	5.2
57.5°	4.2
60°	4.2
62.5°	3.1
65°	3.1
67.5°	3.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)