

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256936

Luminaire Tested: P3AS09R259040DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259040DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 824.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256936
CATALOG NUMBER: P3AS09R259040DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1256936
 CATALOG NUMBER: P3AS09R259040DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	528554
5°	493153
10°	395049
15°	268151
20°	162251
25°	94893
30°	54034
35°	29714
40°	15772
45°	8311
50°	4844
55°	3594
60°	3114
65°	3269
70°	3013
75°	2626
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8311 cd/sqm



TEST NUMBER: P1256936
 CATALOG NUMBER: P3AS09R259040DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.8	24.1
10°-20°	324.7	39.4
20°-30°	185.6	22.5
30°-40°	73.2	8.9
40°-50°	22.5	2.7
50°-60°	8.9	1.1
60°-70°	5.9	0.7
70°-80°	3.3	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.1	86.1
0°-40°	782.3	94.9
0°-60°	813.6	98.7
0°-90°	824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2410	
5°	2240	199
15°	1181	325
25°	392	186
35°	111	73
45°	27	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1256936
CATALOG NUMBER: P3AS09R259040DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2410.4
1°	2405.7
2°	2386.0
3°	2351.4
4°	2303.4
5°	2240.4
6°	2166.3
7°	2082.9
8°	1986.0
9°	1886.8
10°	1774.2
11°	1663.1
12°	1541.1
13°	1420.6
14°	1297.0
15°	1181.2
17.5°	915.8
20°	695.3
22.5°	522.1
25°	392.2
27.5°	290.6
30°	213.4
32.5°	154.3
35°	111.0
37.5°	78.7
40°	55.1
42.5°	37.8
45°	26.8
47.5°	18.9
50°	14.2
52.5°	11.0
55°	9.4
57.5°	8.7
60°	7.1
62.5°	6.3
65°	6.3
67.5°	5.5
70°	4.7
72.5°	3.9
75°	3.1
77.5°	2.4
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8



TEST NUMBER: P1256936
CATALOG NUMBER: P3AS09R259040DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)