

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256947

Luminaire Tested: P3AS09R259040DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1256947  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R259040DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 247.1 lumens  
Efficiency: N/A  
Efficacy: 22.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1256947  
CATALOG NUMBER: P3AS09R259040DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1256947  
 CATALOG NUMBER: P3AS09R259040DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89664
5°	86044
10°	75372
15°	60591
20°	46554
25°	35228
30°	25447
35°	16918
40°	10248
45°	5985
50°	3821
55°	3097
60°	2719
65°	2387
70°	1988
75°	1949
80°	1515
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5985 cd/sqm



TEST NUMBER: P1256947  
 CATALOG NUMBER: P3AS09R259040DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.6	14.4
10°-20°	73.8	29.9
20°-30°	66.7	27.0
30°-40°	40.1	16.2
40°-50°	15.9	6.4
50°-60°	7.3	3.0
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.1	71.3
0°-40°	216.2	87.5
0°-60°	239.5	96.9
0°-90°	247.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	409	
5°	391	36
15°	267	74
25°	146	67
35°	63	40
45°	19	16
55°	8	7
65°	5	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1256947  
CATALOG NUMBER: P3AS09R259040DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	408.9
1°	408.9
2°	407.0
3°	402.8
4°	397.4
5°	390.9
6°	382.4
7°	372.8
8°	361.6
9°	350.4
10°	338.5
11°	324.6
12°	310.4
13°	296.1
14°	281.9
15°	266.9
17.5°	231.4
20°	199.5
22.5°	170.6
25°	145.6
27.5°	122.1
30°	100.5
32.5°	80.9
35°	63.2
37.5°	48.1
40°	35.8
42.5°	26.2
45°	19.3
47.5°	14.6
50°	11.2
52.5°	9.2
55°	8.1
57.5°	6.9
60°	6.2
62.5°	5.0
65°	4.6
67.5°	3.9
70°	3.1
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1256947  
CATALOG NUMBER: P3AS09R259040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)