

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257604

Luminaire Tested: P3AS13R709040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 516.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257604
CATALOG NUMBER: P3AS13R709040DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1257604
 CATALOG NUMBER: P3AS13R709040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99882
5°	98701
10°	95834
15°	91783
20°	85967
25°	78101
30°	67479
35°	53779
40°	39159
45°	25739
50°	12076
55°	3708
60°	3596
65°	3476
70°	3270
75°	3474
80°	3283
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25739 cd/sqm



TEST NUMBER: P1257604
 CATALOG NUMBER: P3AS13R709040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	8.2
10°-20°	113.1	21.9
20°-30°	147.1	28.5
30°-40°	124.8	24.2
40°-50°	64.3	12.5
50°-60°	12.4	2.4
60°-70°	6.7	1.3
70°-80°	4.1	0.8
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.4	58.6
0°-40°	427.2	82.8
0°-60°	504.0	97.7
0°-90°	516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	456	
5°	448	42
15°	404	113
25°	323	147
35°	201	125
45°	83	64
55°	10	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1257604
CATALOG NUMBER: P3AS13R709040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	455.5
2.5°	454.0
5°	448.4
7.5°	440.2
10°	430.4
12.5°	418.1
15°	404.3
17.5°	387.4
20°	368.4
22.5°	346.9
25°	322.8
27.5°	295.7
30°	266.5
32.5°	234.2
35°	200.9
37.5°	168.1
40°	136.8
42.5°	107.6
45°	83.0
47.5°	61.0
50°	35.4
52.5°	15.4
55°	9.7
57.5°	9.2
60°	8.2
62.5°	7.7
65°	6.7
67.5°	6.1
70°	5.1
72.5°	4.6
75°	4.1
77.5°	3.1
80°	2.6
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)