

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256977

Luminaire Tested: P3AS09R309040DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309040DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 641.0 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256977
CATALOG NUMBER: P3AS09R309040DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1256977
 CATALOG NUMBER: P3AS09R309040DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151435
5°	148030
10°	137651
15°	122498
20°	105359
25°	89255
30°	74087
35°	58116
40°	41649
45°	27321
50°	15556
55°	10208
60°	9648
65°	8976
70°	8078
75°	7371
80°	6945
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27321 cd/sqm



TEST NUMBER: P1256977
 CATALOG NUMBER: P3AS09R309040DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	9.7
10°-20°	150.0	23.4
20°-30°	169.1	26.4
30°-40°	135.0	21.1
40°-50°	69.4	10.8
50°-60°	26.1	4.1
60°-70°	17.1	2.7
70°-80°	9.2	1.4
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.5	59.5
0°-40°	516.5	80.6
0°-60°	611.9	95.5
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	691	
5°	672	62
15°	540	150
25°	369	169
35°	217	135
45°	88	69
55°	27	26
65°	17	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1256977
CATALOG NUMBER: P3AS09R309040DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	690.6
1°	690.6
2°	688.2
3°	684.3
4°	678.8
5°	672.5
6°	664.7
7°	654.4
8°	643.4
9°	630.8
10°	618.2
11°	604.1
12°	589.1
13°	573.4
14°	556.9
15°	539.6
17.5°	495.5
20°	451.5
22.5°	409.0
25°	368.9
27.5°	329.6
30°	292.6
32.5°	254.8
35°	217.1
37.5°	180.1
40°	145.5
42.5°	114.8
45°	88.1
47.5°	65.3
50°	45.6
52.5°	32.2
55°	26.7
57.5°	24.4
60°	22.0
62.5°	19.7
65°	17.3
67.5°	14.9
70°	12.6
72.5°	10.2
75°	8.7
77.5°	7.1
80°	5.5
82.5°	3.9
85°	2.4
87.5°	0.8



TEST NUMBER: P1256977
CATALOG NUMBER: P3AS09R309040DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)