

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257650

Luminaire Tested: P3AS17R159040DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159040DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1752.1 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257650

CATALOG NUMBER: P3AS17R159040DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1257650

CATALOG NUMBER: P3AS17R159040DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	95	95	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	93	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	92	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	90	90	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	89	89	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	87	87	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	86	86	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	85	85	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3405473
5°	2854120
10°	1344397
15°	405314
20°	149976
25°	58310
30°	21750
35°	6666
40°	2376
45°	1302
50°	955
55°	1070
60°	1228
65°	726
70°	898
75°	1186
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1302 cd/sqm

TEST NUMBER: P1257650

CATALOG NUMBER: P3AS17R159040DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1002.4	57.2
10°-20°	595.9	34.0
20°-30°	125.2	7.1
30°-40°	20.2	1.2
40°-50°	3.4	0.2
50°-60°	2.5	0.1
60°-70°	1.6	0.1
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1723.4	98.4
0°-40°	1743.6	99.5
0°-60°	1749.6	99.9
0°-90°	1752.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1752.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15530	
5°	12966	###
15°	1785	596
25°	241	125
35°	25	20
45°	4	3
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1257650

CATALOG NUMBER: P3AS17R159040DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	15530.2
1°	15481.7
2°	15235.1
3°	14742.0
4°	14019.0
5°	12966.3
6°	11729.4
7°	10315.1
8°	8964.6
9°	7435.4
10°	6037.8
12.5°	3257.8
15°	1785.4
17.5°	1045.8
20°	642.7
22.5°	393.4
25°	241.0
27.5°	145.4
30°	85.9
32.5°	48.5
35°	24.9
37.5°	13.9
40°	8.3
42.5°	5.5
45°	4.2
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.8
60°	2.8
62.5°	1.4
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)