

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257720

Luminaire Tested: P3AS17R259040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1450.0 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257720
CATALOG NUMBER: P3AS17R259040DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1257720
 CATALOG NUMBER: P3AS17R259040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	930123
5°	867794
10°	695155
15°	471876
20°	285531
25°	166969
30°	95078
35°	52307
40°	27766
45°	14606
50°	8494
55°	6346
60°	5482
65°	5759
70°	5321
75°	4660
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14606 cd/sqm



TEST NUMBER: P1257720
 CATALOG NUMBER: P3AS17R259040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.8	24.1
10°-20°	571.5	39.4
20°-30°	326.5	22.5
30°-40°	128.9	8.9
40°-50°	39.5	2.7
50°-60°	15.6	1.1
60°-70°	10.5	0.7
70°-80°	5.8	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1247.8	86.1
0°-40°	1376.7	94.9
0°-60°	1431.8	98.7
0°-90°	1450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4242	
5°	3942	350
15°	2079	571
25°	690	327
35°	195	129
45°	47	40
55°	17	16
65°	11	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1257720
CATALOG NUMBER: P3AS17R259040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4241.7
1°	4233.4
2°	4198.7
3°	4137.8
4°	4053.2
5°	3942.4
6°	3812.1
7°	3665.2
8°	3494.8
9°	3320.2
10°	3122.0
11°	2926.6
12°	2711.9
13°	2499.8
14°	2282.3
15°	2078.6
17.5°	1611.6
20°	1223.6
22.5°	918.7
25°	690.1
27.5°	511.3
30°	375.5
32.5°	271.6
35°	195.4
37.5°	138.6
40°	97.0
42.5°	66.5
45°	47.1
47.5°	33.3
50°	24.9
52.5°	19.4
55°	16.6
57.5°	15.2
60°	12.5
62.5°	11.1
65°	11.1
67.5°	9.7
70°	8.3
72.5°	6.9
75°	5.5
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	1.4



TEST NUMBER: P1257720
CATALOG NUMBER: P3AS17R259040DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)