

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257724

Luminaire Tested: P3AS17R259040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 545.0 lumens
Efficiency: N/A
Efficacy: 25.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257724

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257724

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129529
5°	126436
10°	117165
15°	104359
20°	89678
25°	76214
30°	62744
35°	48881
40°	35180
45°	22328
50°	13202
55°	9099
60°	8333
65°	7731
70°	6988
75°	6354
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22328 cd/sqm

TEST NUMBER: P1257724

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	9.8
10°-20°	127.6	23.4
20°-30°	144.2	26.5
30°-40°	114.0	20.9
40°-50°	57.6	10.6
50°-60°	23.1	4.2
60°-70°	14.8	2.7
70°-80°	8.2	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.1	59.6
0°-40°	439.1	80.6
0°-60°	519.8	95.4
0°-90°	545.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	591	
5°	574	53
15°	460	128
25°	315	144
35°	183	114
45°	72	58
55°	24	23
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1257724

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	590.7
1°	590.7
2°	588.7
3°	585.3
4°	580.5
5°	574.4
6°	566.9
7°	558.1
8°	548.6
9°	537.7
10°	526.2
11°	513.3
12°	501.1
13°	486.8
14°	473.2
15°	459.7
17.5°	421.6
20°	384.3
22.5°	349.0
25°	315.0
27.5°	281.8
30°	247.8
32.5°	215.9
35°	182.6
37.5°	152.1
40°	122.9
42.5°	95.7
45°	72.0
47.5°	53.6
50°	38.7
52.5°	29.2
55°	23.8
57.5°	21.7
60°	19.0
62.5°	17.0
65°	14.9
67.5°	12.9
70°	10.9
72.5°	9.5
75°	7.5
77.5°	6.1
80°	4.8
82.5°	3.4
85°	2.0
87.5°	0.7



TEST NUMBER: P1257724

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)