

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257726

Luminaire Tested: P3AS17R259040DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1112.0 lumens
Efficiency: N/A
Efficacy: 52.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257726

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1257726

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264277
5°	257979
10°	239051
15°	212918
20°	182973
25°	155525
30°	128020
35°	99769
40°	71763
45°	45524
50°	26950
55°	18542
60°	17016
65°	15825
70°	14233
75°	12878
80°	12249
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45524 cd/sqm

TEST NUMBER: P1257726

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	9.8
10°-20°	260.4	23.4
20°-30°	294.2	26.5
30°-40°	232.7	20.9
40°-50°	117.5	10.6
50°-60°	47.1	4.2
60°-70°	30.1	2.7
70°-80°	16.6	1.5
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.2	59.6
0°-40°	895.9	80.6
0°-60°	1060.5	95.4
0°-90°	1112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1205	
5°	1172	109
15°	938	260
25°	643	294
35°	373	233
45°	147	118
55°	48	47
65°	30	30
75°	15	17
85°	4	5
90°	0	

TEST NUMBER: P1257726

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1205.2
1°	1205.2
2°	1201.1
3°	1194.1
4°	1184.4
5°	1172.0
6°	1156.7
7°	1138.7
8°	1119.3
9°	1097.2
10°	1073.6
11°	1047.3
12°	1022.4
13°	993.3
14°	965.6
15°	937.9
17.5°	860.3
20°	784.1
22.5°	712.1
25°	642.8
27.5°	574.9
30°	505.6
32.5°	440.5
35°	372.7
37.5°	310.3
40°	250.7
42.5°	195.3
45°	146.8
47.5°	109.4
50°	79.0
52.5°	59.6
55°	48.5
57.5°	44.3
60°	38.8
62.5°	34.6
65°	30.5
67.5°	26.3
70°	22.2
72.5°	19.4
75°	15.2
77.5°	12.5
80°	9.7
82.5°	6.9
85°	4.2
87.5°	1.4



TEST NUMBER: P1257726

CATALOG NUMBER: P3AS17R259040DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)