

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257730

Luminaire Tested: P3AS17R259040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 435.0 lumens
Efficiency: N/A
Efficacy: 20.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257730

CATALOG NUMBER: P3AS17R259040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257730

CATALOG NUMBER: P3AS17R259040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157926
5°	151507
10°	132730
15°	106698
20°	81977
25°	62012
30°	44817
35°	29767
40°	18062
45°	10513
50°	6720
55°	5429
60°	4780
65°	4203
70°	3462
75°	3474
80°	2526
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10513 cd/sqm

TEST NUMBER: P1257730

CATALOG NUMBER: P3AS17R259040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.7	14.4
10°-20°	130.0	29.9
20°-30°	117.5	27.0
30°-40°	70.6	16.2
40°-50°	28.1	6.4
50°-60°	12.9	3.0
60°-70°	7.9	1.8
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.1	71.3
0°-40°	380.7	87.5
0°-60°	421.7	96.9
0°-90°	435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	720	
5°	688	63
15°	470	130
25°	256	118
35°	111	71
45°	34	28
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1257730

CATALOG NUMBER: P3AS17R259040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	720.2
1°	720.2
2°	716.8
3°	709.4
4°	699.9
5°	688.3
6°	673.4
7°	656.5
8°	636.8
9°	617.1
10°	596.1
11°	571.7
12°	546.6
13°	521.5
14°	496.4
15°	470.0
17.5°	407.6
20°	351.3
22.5°	300.4
25°	256.3
27.5°	215.0
30°	177.0
32.5°	142.4
35°	111.2
37.5°	84.8
40°	63.1
42.5°	46.1
45°	33.9
47.5°	25.8
50°	19.7
52.5°	16.3
55°	14.2
57.5°	12.2
60°	10.9
62.5°	8.8
65°	8.1
67.5°	6.8
70°	5.4
72.5°	4.7
75°	4.1
77.5°	3.4
80°	2.0
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1257730

CATALOG NUMBER: P3AS17R259040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)