

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257064

Luminaire Tested: P3AS09R459040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257064
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 278.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257064

CATALOG NUMBER: P3AS09R459040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1257064

CATALOG NUMBER: P3AS09R459040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82800
5°	80915
10°	74637
15°	64904
20°	53321
25°	41494
30°	30638
35°	21549
40°	13454
45°	7288
50°	3957
55°	3403
60°	3026
65°	2594
70°	2244
75°	2288
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7288 cd/sqm

TEST NUMBER: P1257064

CATALOG NUMBER: P3AS09R459040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	12.2
10°-20°	79.0	28.4
20°-30°	78.5	28.2
30°-40°	50.5	18.2
40°-50°	19.5	7.0
50°-60°	7.9	2.8
60°-70°	5.0	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.6	68.9
0°-40°	242.1	87.1
0°-60°	269.5	96.9
0°-90°	278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	378	
5°	368	34
15°	286	79
25°	172	78
35°	80	51
45°	24	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1257064

CATALOG NUMBER: P3AS09R459040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	377.6
2.5°	375.7
5°	367.6
7.5°	353.7
10°	335.2
12.5°	312.1
15°	285.9
17.5°	257.4
20°	228.5
22.5°	199.2
25°	171.5
27.5°	145.3
30°	121.0
32.5°	99.8
35°	80.5
37.5°	63.2
40°	47.0
42.5°	33.9
45°	23.5
47.5°	15.8
50°	11.6
52.5°	9.6
55°	8.9
57.5°	7.7
60°	6.9
62.5°	5.8
65°	5.0
67.5°	4.2
70°	3.5
72.5°	3.1
75°	2.7
77.5°	1.9
80°	1.5
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)