

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257736

Luminaire Tested: P3AS17R259040DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259040DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1473.0 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257736

CATALOG NUMBER: P3AS17R259040DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1257736

CATALOG NUMBER: P3AS17R259040DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	102		101
2	113	109	107	105	111	108	105	103	105	103	101		102	100	99		99
3	110	106	103	100	108	104	102	99	102	100	98		100	98	96		98
4	107	103	99	97	106	102	99	96	100	97	95		98	96	94		96
5	105	100	96	94	103	99	96	93	97	95	93		96	94	92		95
6	102	97	94	91	101	97	93	91	95	93	91		94	92	90		93
7	100	95	92	89	99	95	91	89	94	91	89		93	90	88		92
8	98	93	90	87	98	93	89	87	92	89	87		91	88	87		90
9	97	91	88	86	96	91	88	85	90	87	85		89	87	85		89
10	95	89	86	84	94	89	86	84	88	86	84		88	85	83		87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2252868
5°	1924120
10°	1213093
15°	564589
20°	116257
25°	23711
30°	5064
35°	1071
40°	573
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1257736

CATALOG NUMBER: P3AS17R259040DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	728.5	49.5
10°-20°	676.6	45.9
20°-30°	64.0	4.3
30°-40°	3.7	0.3
40°-50°	0.2	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1469.1	99.7
0°-40°	1472.8	100.0
0°-60°	1473.0	100.0
0°-90°	1473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1473.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10274	
5°	8741	728
15°	2487	677
25°	98	64
35°	4	4
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1257736

CATALOG NUMBER: P3AS17R259040DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10273.9
2.5°	9891.8
5°	8741.3
7.5°	7186.8
10°	5448.1
12.5°	3935.5
15°	2487.0
17.5°	1202.5
20°	498.2
22.5°	198.1
25°	98.0
27.5°	46.0
30°	20.0
32.5°	8.0
35°	4.0
37.5°	2.0
40°	2.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)