

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257090

Luminaire Tested: P3AS09R509040DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509040DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 690.1 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257090
CATALOG NUMBER: P3AS09R509040DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1257090
 CATALOG NUMBER: P3AS09R509040DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	8.5
10°-20°	150.2	21.8
20°-30°	182.5	26.4
30°-40°	154.8	22.4
40°-50°	80.4	11.7
50°-60°	29.0	4.2
60°-70°	20.1	2.9
70°-80°	10.9	1.6
80°-90°	3.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.5	56.7
0°-40°	546.2	79.2
0°-60°	655.7	95.0
0°-90°	690.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	640	
5°	628	59
15°	539	150
25°	399	182
35°	249	155
45°	104	80
55°	32	29
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1257090
CATALOG NUMBER: P3AS09R509040DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	639.5
2.5°	637.1
5°	627.6
7.5°	613.5
10°	593.0
12.5°	567.0
15°	538.7
17.5°	506.4
20°	470.9
22.5°	434.7
25°	399.3
27.5°	362.3
30°	324.5
32.5°	286.7
35°	248.9
37.5°	211.8
40°	174.8
42.5°	139.4
45°	104.0
47.5°	69.3
50°	44.9
52.5°	34.7
55°	31.5
57.5°	28.4
60°	26.0
62.5°	22.8
65°	20.5
67.5°	17.3
70°	15.0
72.5°	12.6
75°	10.2
77.5°	7.9
80°	6.3
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)