

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1257096

Luminaire Tested: P3AS09R509040DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1257096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509040DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 581.0 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1257096

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1257096

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68		
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64		
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60		
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56		
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168978
5°	164428
10°	151634
15°	133349
20°	111566
25°	88481
30°	64896
35°	44624
40°	28367
45°	15847
50°	8597
55°	7226
60°	6228
65°	5707
70°	5065
75°	4660
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15847 cd/sqm

TEST NUMBER: P1257096

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	11.9
10°-20°	162.7	28.0
20°-30°	166.4	28.6
30°-40°	105.5	18.2
40°-50°	42.0	7.2
50°-60°	17.0	2.9
60°-70°	10.9	1.9
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	398.3	68.6
0°-40°	503.8	86.7
0°-60°	562.8	96.9
0°-90°	581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	771	
5°	747	69
15°	587	163
25°	366	166
35°	167	106
45°	51	42
55°	19	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1257096

CATALOG NUMBER: P3AS09R509040DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	770.6
2.5°	765.1
5°	747.0
7.5°	718.7
10°	681.0
12.5°	636.2
15°	587.4
17.5°	533.9
20°	478.1
22.5°	422.3
25°	365.7
27.5°	309.0
30°	256.3
32.5°	209.2
35°	166.7
37.5°	130.5
40°	99.1
42.5°	73.1
45°	51.1
47.5°	34.6
50°	25.2
52.5°	21.2
55°	18.9
57.5°	16.5
60°	14.2
62.5°	12.6
65°	11.0
67.5°	9.4
70°	7.9
72.5°	6.3
75°	5.5
77.5°	3.9
80°	3.1
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)